



|  |                           |                             |                                  |
|--|---------------------------|-----------------------------|----------------------------------|
|  | Kohle-Schichtwid. 0,25 W  | Carbon film resistor 0,25 W | Resistance à couche carb. 0,25 W |
|  | Metall-Schichtwid. 0,25 W | Metal film resistor 0,25 W  | Resistance à film métall. 0,25 W |
|  | Metall-Schichtwid. 0,5 W  | Metal film resistor 0,5 W   | Resistance à film métall. 0,5 W  |
|  | Spulenwid.                | Coil resistor               | Resistance bobinée               |

|  |                        |                           |                                   |
|--|------------------------|---------------------------|-----------------------------------|
|  | Shunt (Manganin-Draht) | Shunt (manganin wire)     | Shunt (fil de manganine)          |
|  | Kohle-Potentiometer    | Carbon film potentiometer | Potentiomètre à couche de carbone |
|  | Prüfpunkt              | Testing point             | Point de test                     |

k = kΩ

M MΩ

m mΩ

mΩ